



## Commercial status

This Product is Obsolete :

 This Product is Obsolete

## Main

Range of product	TeSys D
Range	TeSys
Product or component type	Contacteur coil
Device short name	LX4D7
Control circuit type	DC standard
[Uc] control circuit voltage	543 V DC
Average resistance	14058 Ohm at 68 °F (20 °C)
Product compatibility	LC1D80
Mechanical durability	10 Mcycles
Operating rate	3600 cyc/h at <= 140 °F (60 °C)

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.1...0.3 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Time constant	75 ms
Inrush power in W	22 W at 68 °F (20 °C)
Hold-in power consumption in W	22 W at 68 °F (20 °C)

## Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Product weight	1.5 lb(US) (0.68 kg)

### Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5
Returnability	N
Country of origin	FR

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1624 - Schneider Electric declaration of conformity <a href="#">Schneider-Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**