

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 519.00 USD



## Commercial status

This Product is Obsolete :

 This Product is Obsolete

## Main

Range of product	C60
Range	Multi 9
Product name	Multi 9 C60
Product or component type	Miniature circuit-breaker
Device short name	C60 UL489
Device application	Distribution
Poles description	3P
Number of protected poles	3
[In] rated current	6 A at 77 °F (25 °C)
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity code	N
Breaking capacity	AIR 10 kA at 480Y/277 V AC conforming to UL 489 AIR 10 kA at 480Y/277 V AC conforming to CSA C22.2 No 5.2 Icu 10 kA at 480Y/277 V AC conforming to EN/IEC 60947-2 Icu 10 kA at 480Y/277 V AC conforming to GB 14048.2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

## Complementary

Network frequency	50/60 Hz
System Voltage	480Y/277 V AC
Magnetic tripping limit	8.5 x In +/- 20% AC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle

Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Connection pitch	0.71 in (18 mm) Between phases
9 mm pitches	6
Height	5.55 in (141 mm)
Width	2.13 in (54 mm)
Depth	68.7 mm
Product weight	0.73 lb(US) (0.33 kg)
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Ring terminal, top or bottom
Tightening torque	17.7 lbf.in (2 N.m) top or bottom
Compatibility code	C60UL489

## Environment

Standards	UL 489 CSA C22.2 No 5 GB 14048.2 EN/IEC 60947-2
Product certifications	UL CSA CCC IEC
IP degree of protection	IP40 modular enclosure conforming to IEC 60529 IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % 131 °F (55 °C)
Operating altitude	6561.68 ft (2000 m)
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

## Ordering and shipping details

Category	00915 - C60N MINIATURE CIRCUIT BREAKER-UL489
Discount Schedule	DE2
GTIN	00785901861928
Nbr. of units in pkg.	1
Package weight(Lbs)	1.03
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity <a href="#">Schneider-Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	<b>End of commercialisation</b>
-----------------------	---------------------------------

## MGN61394 may be replaced by any of the following products:



**M9F52306**

Multi 9 - C60BPR - MCB - 3P - 6 A - C Curve - 480Y/277 V - 10 kA - UL 489

Qty 1

Reason for Substitution: End of life | Substitution date: 29 Apr 2019 |