



Commercial status

End of Commercialisation :

⚠ End of Commercialisation

Main

Range	Unica
Aesthetic name	Unica Top - Unica Class
Product or component type	Key card switch
Device application	Control
Device presentation	Mechanism with zamak fixing frame + long claws
Cover plate colour tint	Aluminium

Complementary

[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Rated current	10 A
Load type	230 V AC incandescent lamp - 1470 W 230 V AC halogen lamp - 1470 W 230 V AC fan - 1470 W 230 V AC convector - 1470 W Low voltage halogen lamp with ferromagnetic transformer - 1000 VA Low voltage halogen lamp with electronic transformer - 1470 VA Fluorescent tube ferromagnetic ballast - 1470 VA Compact fluorescent lamp - 1470 W LED lamp - 1470 W Contactor
Condition of use	Control through appropriate relay
Actuator	Card 54 x 86 x 0.85 mm (maximum)
Number of modules	2 modules
Fuse type	Electronic
Maximum number of switchings	50000 operations
Pilot light	Locator lamp
Marking	Vertical insertion pictogram
Connections - terminals	Soldered connectors
Clamping connection capacity	<= 1 x 2.5 mm ² for flexible cable(s) <= 1 x 2.5 mm ² for rigid cable(s)
Fixing mode	Long claws
Material	ASA + PC: mechanism cover Zamak: fixing frame
Embedding depth	14 Mm
Depth	Unica Top cover frame: 35 mm Unica Class cover frame: 35 mm
Width	70.9 Mm
Height	70.9 Mm
Net weight	0.0689 Kg

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	5...30 °C
Ambient air temperature for storage	-20...60 °C
Environmental characteristic	Oil Acetone Bleach Petrol UV resistant Ammonia Liquid soap Alcohol Window-cleaning fluid
Environmental health and issues	Halogen free
Standards	EN 61058-1

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**