

Main

Range of product	Minera
Product or component type	Oil type transformer
Network type	AC
Type of installation	Indoor
Product certifications	IEC
Relay type	1 DMCR relay

Complementary

Type of cooling	ONAN (oil natural air natural)
Rated power in VA	400 kVA
Network frequency	50 Hz
Electrical insulation class	A
Network number of phases	3 phases
Primary voltage	20 kV
Locking options description	Without keylocks high voltage connection
Isolation voltage	Secondary: 1.1 kV AC Primary: 24 kV AC
[Ui] rated insulation voltage	Secondary circuit : 10 V AC Primary circuit : 50 V AC
[Uimp] rated impulse withstand voltage	125 kV
Secondary voltage	410 V at no load
Vector group	Dyn11
Tapping range	+/- 2 x 2.5 %
Number of steps	5
Temperature rise	65 K (oil)
Percentage impedance voltage	4 %
No load losses	430 W
Thermal losses	4600 W at 120 °C
Operating altitude	< 1000 m
Material	Aluminium
Mounting mode	Fixed
Mounting support	Floor
IP degree of protection	IP21 optional MINBAC04000800 low voltage cable box IP00 enclosure IEC
Product weight	1345 kg 273 kg insulation
Height	1553 mm
Width	890 mm

Length	1270 mm
Noise level	40 dB at 1 m

Environment

Ambient air temperature for operation	-20...40 °C
Ambient air temperature for storage	-20...40 °C
Relative humidity	0...95 %

Product Life Status : **Commercialised**