



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

| | |
|--------------------------------|--|
| Range | TeSys |
| Product name | TeSys F |
| Product or component type | Contactor |
| Device short name | LC1F |
| Contactor application | Resistive load |
| Utilisation category | AC-1 |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | <= 1000 V AC 50/60 Hz <= 460 V DC |
| [Ie] rated operational current | 1700 A (at <40 °C) at <= 440 V AC AC-1 |
| [Uc] control circuit voltage | 440 V AC 40...400 Hz |

Complementary

| | |
|---|--|
| [Uimp] rated impulse withstand voltage | 8 KV |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 1700 A (at 40 °C) |
| Rated breaking capacity | 2550 A conforming to IEC 60947-4-1 |
| [Icw] rated short-time withstand current | 10000 A 40 °C - 10 s 7500 A 40 °C - 30 s 5500 A 40 °C - 1 min 4200 A 40 °C - 3 min 3000 A 40 °C - 10 min |
| Associated fuse rating | 1600 A gG at <= 440 V |
| Average impedance | 0.1 MOhm - Ith 1700 A 50 Hz |
| [Ui] rated insulation voltage | 1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C |
| Power dissipation per pole | 200 W AC-1 |
| Mounting support | Plate |
| Standards | EN 60947-1 JIS C8201-4-1 EN 60947-4-1 IEC 60947-4-1 IEC 60947-1 |
| Product certifications | CCC CETLus CB CSA |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|---------------------------------|--|
| Connections - terminals | Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² solid without cable end Power circuit: bar 3 cable(s) - busbar cross section: 100 x 5 mm Power circuit: bolted connection |
| Tightening torque | Control circuit: 1.2 N.m Power circuit: 58 N.m |
| Control circuit voltage limits | Operational: 0.85...1.1 U _c 40...400 Hz (at 55 °C) Drop-out: 0.3...0.5 U _c 40...400 Hz (at 55 °C) |
| Inrush power in VA | 2200 VA 40...400 Hz cos phi 0.9 (at 20 °C) |
| Hold-in power consumption in VA | 36 VA 40...400 Hz cos phi 0.9 (at 20 °C) |
| Heat dissipation | 36 W |
| Operating time | 100...170 ms opening 40...75 ms closing |
| Maximum operating rate | 600 Cyc/H 55 °C |
| Compatibility code | LC1F |

Environment

| | |
|---|----------------|
| Protective treatment | TH |
| Ambient air temperature for operation | -5...40 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...60 °C |
| Operating altitude | 3000 m without |
| Height | 332 Mm |
| Width | 438 Mm |
| Depth | 238.6 Mm |
| Net weight | 30 Kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **End of commercialisation**