



## Main

Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism
Socket number	2
Outlet poles configuration	2P + E with shutters
Outlet standard	German
Outlet standard description	Side earth
Ground lug position	45° ground lug

## Complementary

Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	4 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)
Pilot light	Red red indicator lamp : 1.5 mA
Connections - terminals	IPT (Isolates Piercing Terminal) Screw terminals
Cable cross section	0...2.5 mm <sup>2</sup> cable(s), 2 - cable stiffness: flexible 0...2.5 mm <sup>2</sup> cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I <sub>n</sub> and 1.1 I <sub>un</sub> , cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : PC
Surface finish	Matt
Quantity per set	Flow-pack : set of 1
Standards	IEC 60884-1 DIN VDE 0620-1 UNE 20315-1-1 UNE 20315-1-2
Product certifications	Aenor EAC
Embedding depth	31.1 mm
Depth	40.4 mm
Width	45 mm
Height	90 mm

Product weight	0.079 kg
Surface treatment	Painted

### Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Ammonia Acetone Liquid soap UV resistant Window-cleaning fluid Petrol Oil Alcohol Bleach
Environmental health and issues	Halogen free

### Offer Sustainability

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**