



### Main

Range of product	New Unica
Range	New Unica
Device application	Control
Product or component type	Switch
Device presentation	Mechanism
Switch function	2-pole 1-way
Colour tint	White (RAL 9003)
Quantity per set	10 flow-pack

### Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Pilot light	Red LED : 1.5 mA
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> (rigid) 0...4 mm <sup>2</sup> (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn5 Ag
Marking	0 - 1
Surface finish	Glossy
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	37.75 mm
Embedding depth	24.65 mm
Product weight	0.0223 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	RoHS compliant LV directive IEC 60669-1

Product certifications	EAC CE Aenor NF
Targeted channel	Professional
Main colour tint	White

### Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Window-cleaning fluid Oil UV resistant Petrol Ammonia Bleach Liquid soap Acetone Alcohol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**