



Main

Range	New Unica
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 2-way
Device application	Control
Colour tint	Anthracite (RAL 7021)
Quantity per set	10 flow-pack

Complementary

Rated current	16 AX at 250 V AC 50/60 Hz
Electrical durability	20000 Cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Pilot light	Without LED
Connections - terminals	Screw terminals
Cable cross section	0...4 Mm ² rigid cable 0...4 Mm ² flexible cable
Material	CuZn15: fixed terminals CuZn5 Ag: mobile contact Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing
Marking	Without marking
Surface finish	Painted powder coated
Fixing mode	Clip-in
Width	22.5 Mm
Height	45 Mm
Depth	34.25 Mm
Embedding depth	21.15 Mm
Net weight	0.0179 Kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Standards	RoHS compliant IEC 60669-1 LV directive
Product certifications	CE Aenor EAC NF

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Alcohol Liquid soap Acetone Window-cleaning fluid UV resistant Bleach Oil Petrol Ammonia
Environmental health and issues	Halogen free

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**