

Product data sheet

Characteristics

LE3D326Q7

TeSys LE - enclosed star-delta starter - 32 A -
380 V AC coil

Commercial status

End of Commercialisation :

△ End of Commercialisation

Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Star-delta contactors
Motor power kW	15 kW at 220 V AC 50/60 Hz 30 kW at 380/400 V AC 50/60 Hz 30 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	380 V AC 50/60 Hz
Associated fuse rating	63 A 14 x 51 mm aM
Control type	Without

Complementary

Width	287 mm
Height	367 mm
Depth	190 mm
Product weight	7.65 kg

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.