



Main

Range	New Unica
Device application	Control
Product or component type	Push-button switch
Device presentation	Mechanism
Colour tint	Aluminium
Quantity per set	10 flow-pack

Complementary

Rated current	10 A, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	White LED : 0.05 mA
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Without marking
Surface finish	Painted powder coated
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34.25 mm
Embedding depth	21.15 mm
Product weight	0.0252 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	LV directive RoHS compliant IEC 60669-1
Product certifications	Aenor CE EAC NF

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	UV resistant Window-cleaning fluid Oil Alcohol Liquid soap Acetone Ammonia Petrol Bleach
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**