



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 7103.31 USD



### Main

Range of product	PacDrive 3
Product or component type	Motion controller

### Complementary

Product compatibility	LMC802
Number of axis	<= 130
Discrete input number	20 digital input conforming to IEC 61131-2 Type 1 4 interrupt input conforming to IEC 61131-2 Type 1 16 touch probe input conforming to IEC 61131-2 Type 1
Discrete input voltage	0...6 V 20...33 V
Discrete input voltage type	DC
Analogue input number	2
Analogue input type	Voltage analog input: - 10...10 V Current analog input: - 20...20 mA
Analogue input resolution	12 bits
Discrete input current	5 mA digital input 5 mA interrupt input 5 mA touch probe input
Input impedance	100000 Ohm analog input 500 Ohm
Anti bounce filtering	Configurable from 1 ms or 5 ms digital input From 100 µs touch probe input Configurable from 0.1 ms or 1 ms interrupt input
Discrete output number	16 digital output 2 analog output
Discrete output current	250 mA for digital output
Leakage current	< 0.4 mA
Number of I/O expansion module	2
[Us] rated supply voltage	24 V DC
Power consumption in W	36 W

Memory type	NVRAM 256 kB RAM DDR3L 1 GB
Programming language	SFC (sequential function chart) IL (instruction list) FBD (function block diagram) CFC (continuous function chart) LD (ladder) ST (structured text)
Integrated connection type	2 Ethernet port, connector RJ45 for protocol Sercos 1 CAN port, connector SUB-D 9 for protocol CANopen 1 USB port, connector USB type A 2 Ethernet port, connector RJ45 for protocol RT-Ethernet (real-time) 1 Ethernet port, connector RJ45 for protocol PacNet 1 port, connector SUB-D 9 for protocol Profibus DP 1 COM1 serial link, connector SUB-D 9 for protocol RS232 1 COM2 serial link, connector SUB-D 9 for protocol RS422/RS485 1 port, connector SUB-D 9 master encoder 1 Ethernet port, connector RJ45 for protocol Ethernet 10/100/1000BASE-T, FT-P/HTTP
Supply	Power supply 24 V DC, 1 A
Width	3.94 in (100 mm)
Height	12.2 in (310 mm)
Depth	9.57 in (243 mm)
Product weight	7.72 lb(US) (3.5 kg)


## Environment

Standards	CSA C22.2 No 14 CSA C22.2 No 274 UL 508C EN/IEC 61131-2
Product certifications	CE CULus CSA EAC
Ambient air temperature for operation	41...131 °F (5...55 °C)
Relative humidity	5...95 % without condensation
IP degree of protection	IP20 conforming to EN/IEC 60529
Pollution degree	2 conforming to IEC 61131-2
Vibration resistance	3.5 mm (f = 5...8.4 Hz) 10 m/s <sup>2</sup> (f = 8.4...150 Hz)
Shock resistance	150 m/s <sup>2</sup> (duration = 6 ms) conforming to EN/IEC 60721-3-3 operation

## Ordering and shipping details

Category	18354 - PACDRIVE3 MOTION CONTROLLERS
Discount Schedule	PC52
Nbr. of units in pkg.	1
Package weight(Lbs)	9
Returnability	N
Country of origin	DE

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1606 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:

----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Product Life Status : **Commercialised**