

Main

Range of product	New Unica
Range	New Unica
Device application	Key-card switch
Product or component type	Switch
Device presentation	Mechanism
Switch function	2-way and OFF retractive
Colour tint	Aluminium
Quantity per set	10 flow-pack

Complementary

Rated current	10 A, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Access card
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Card
Surface finish	Painted powder coated
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	39.95 mm
Embedding depth	21.15 mm
Product weight	0.0323 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	IEC 60669-1 LV directive RoHS compliant

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Product certifications	CE EAC Aenor NF
Targeted channel	Professional
Main colour tint	Aluminium

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Acetone Window-cleaning fluid Ammonia UV resistant Petrol Bleach Alcohol Oil Liquid soap
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**