



Main

| | |
|---------------------------|-----------------------------------|
| Range | New Unica |
| Product or component type | RJ45 connector |
| Device application | Communication |
| Device presentation | Mechanism |
| Colour tint | White (RAL 9003) |
| Data socket type | RJ45 8 contact(s) Cat.6 < 250 MHz |
| Provided equipment | Label holder Protective flap |

Complementary

| | |
|-----------------------------|------------------------------------------------|
| Communication network type | 1000BASE-TX |
| Communication port protocol | ATM 1200 Mbps |
| Number of modules | 2 modules |
| Socket number | 1 |
| Type of footprint | Infraplus |
| Connector type | S-One |
| Cable shielding type | U/UTP |
| Organization of wire | Unshielded twisted pair |
| Connections - terminals | Click |
| Device mounting | Flush |
| Fixing mode | Clip-in |
| Material | Thermoplastic ABS-UV stabilised: central plate |
| Depth | 40.5 Mm |
| Width | 45 Mm |
| Height | 45 Mm |
| Embedding depth | 40.5 Mm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

| | |
|---------------------------------------|------------------------------------------------------------------------------------------------------------------|
| IP degree of protection | IP20 |
| IK degree of protection | IK01 |
| Ambient air temperature for operation | -25...55 °C |
| Ambient air temperature for storage | -25...55 °C |
| Environmental characteristic | Petrol Ammonia Bleach Window-cleaning fluid UV resistant Liquid soap Acetone Alcohol Oil |
| Environmental health and issues | Halogen free |

Offer Sustainability

| | |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Product Life Status : **Commercialised**