



Main

Range	New Unica
Device application	Signalling
Product or component type	Buzzer
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC, 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Aluminium

Complementary

Current consumption	40 mA
Type of setting	Volume can be adjusted using a screw
Operating time	<= 30 ms
Connections - terminals	Screw terminals
Acoustic level	Between 76 and 80 dB
Cable cross section	0.75...1.5 mm ² (flexible) 0.75...1.5 mm ² (rigid)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised
Standards	EN 62080 CE
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 mm
Depth	50 mm
Width	45 mm
Height	45 mm
Product weight	0.091 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IK degree of protection	IK04
IP degree of protection	IP20
Environmental characteristic	Liquid soap Acetone Petrol UV resistant Ammonia Window-cleaning fluid Alcohol Bleach Oil
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**