



Main

Range	Compact
Product name	Compact NSXm Micrologic Vigi 4.1
Device short name	NSXm 100H
Product or component type	Earth leakage circuit breaker
Device application	Protection Distribution

Complementary

[In] rated current	100 A
Poles description	3P 3d
Neutral position	Left
Control type	Toggle
Mounting mode	By screws (plate) Clip-on (DIN rail)
Network type	AC
Network frequency	50/60 Hz
Breaking capacity code	H 70 kA 415 V AC
Breaking capacity	Icu 100 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 Icu 70 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 Icu 65 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Ue] rated operational voltage	440 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	100 KA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 70 KA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 KV IEC 60947-2
[Ui] rated insulation voltage	500 V conforming to IEC 60947-2
Trip unit technology	Electronic
Trip unit name	Micrologic 4.1
Trip unit protection functions	LSolR
Trip unit rating	100 A at 40 °C
Protection type	Instantaneous short-circuit protection Earth-leakage protection Short time short-circuit protection Overload protection (long time)
Thermal memory	20 minutes before and after tripping
Long time pick-up adjustment range	0.4...1 x In

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

[tr] long-time delay adjustment range	5 S at 7.2 x Ir 8 S at 6 x Ir 200 S at 1.5 x Ir
Short-time pick-up adjustment type Isd	Adjustable 9 settings
[Isd] short-time pick-up adjustment range	1.5...10 x Ir
Short-time delay adjustment type	Fixed
Instantaneous pick-up adjustment range	1500 A
Earth-leakage sensitivity	30 MA for class A 100 MA for class A 300 MA for class A 500 MA for class A 1000 MA for class A 30 MA for class AC 100 MA for class AC 300 MA for class AC 500 MA for class AC 1000 MA for class AC 3000 MA for class AC 5000 MA for class AC
[IΔn] residual earth-leakage sensitive adjustment	1 A 5 A 500 MA 3 A 100 MA 30 MA 300 MA
[Δt] residual earth-leakage time delay adjustment	0 Ms 60 Ms 150 Ms 500 Ms 1000 Ms
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
9 mm pitches	9 module
Connection pitch	35 Mm with spreaders 27 Mm without spreaders
Connections - terminals	1 Everlink lug wire size 2.5...70 mm ² , fine stranded copper 1 Everlink lug wire size 2.5...95 mm ² , rigid or stranded aluminium/copper
Tightening torque	5 N.M for 2.5...10 mm ² 9 N.M for 16...95 mm ²
Local signalling	Flag (green)presence of auxiliary contacts:
Number of slots	1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX
Wire stripping length	20 Mm

Environment

Quality labels	CE
Standards	EN/IEC 60947
Product certifications	CCC EAC
Colour	Grey (RAL 7016)
IP degree of protection	Front cover: IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	2000 m without derating 5000 m with derating
Mechanical durability	20000 Cycles conforming to IEC 947-1 Annex K ed 5.2 In
Electrical durability	10000 Cycles conforming to IEC 947-1 Annex F ed 5.2 for In at 440 V
Height	144 Mm
Width	108 Mm
Depth	80 Mm
Net weight	1.63 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**