



Main

Range of product	INF100...160
Range	Fupact
Product name	Fupact INF
Device short name	INFB100
Product or component type	Switch-disconnector-fuse
Device application	Protection
Poles description	4P
Protected poles description	3f
Fuse type	BS
Fuse size	A2 A3 A4
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Control type	Without handle
Rotary handle mounting location	Front
Rotary handle mounting style	Extended Direct
Provision for padlocking	Padlockable
Mounting mode	Vertical - horizontal
Mounting support	DIN rail, with specific accessories Mounting plate
[Ie] rated operational current	AC-22A: 100 A AC 50/60 Hz 220/240 V AC-22A: 100 A AC 50/60 Hz 380/415 V AC-22A: 100 A AC 50/60 Hz 440/480 V AC-22A: 100 A AC 50/60 Hz 500/525 V AC-22A: 100 A AC 50/60 Hz 660/690 V AC-23A: 100 A AC 50/60 Hz 220/240 V AC-23A: 100 A AC 50/60 Hz 380/415 V AC-23A: 100 A AC 50/60 Hz 440/480 V AC-23A: 100 A AC 50/60 Hz 500/525 V DC-21B: 100 A DC 440 V 4 poles in series AC-23A: 100 A AC 50/60 Hz 660/690 V DC-23B: 100 A DC 220 V 2 poles in series DC-22B: 100 A DC 220 V 2 poles in series

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

[Ith] conventional free air thermal current	100 A (40 °C) vertical 80 A (60 °C) vertical 85 A (55 °C) vertical 71 A (70 °C) horizontal 76 A (65 °C) horizontal 71 A (70 °C) vertical 80 A (60 °C) horizontal 76 A (65 °C) vertical 85 A (55 °C) horizontal 89 A (50 °C) horizontal 89 A (50 °C) vertical 93 A (45 °C) horizontal 96 A (40 °C) horizontal 93 A (45 °C) vertical 100 A (35 °C) horizontal
[Ithe] conventional enclosed thermal current	100 A at 40 °C, Power dissipation per fuse: 12 W (300 mm x 350 mm x 200 mm)
Maximum power	30 KW at 220/240 V AC 50/60 Hz 45 KW at 380/400 V AC 50/60 Hz 55 KW at 415 V AC 50/60 Hz 60 KW at 500/525 V AC 50/60 Hz 90 KW at 660/690 V AC 50/60 Hz
Rated duty	Uninterrupted
Intermittent duty class	Class 120 - 60 %
[Ui] rated insulation voltage	1000 V AC 50/60 Hz 1000 V DC
[Uimp] rated impulse withstand voltage	12 KV
[Ue] rated operational voltage	690 V AC 50/60 Hz 690 V AC 50/60 Hz AC-20 690 V DC DC-20 500 V DC
[Im] rated making and breaking capacity	Icm 105 kA at 690 V conforming to DIN (with fuse) Icm 176 kA at 415 V conforming to BS (with fuse) Icm 220 kA at 500 V conforming to DIN (with fuse) Icn 100 kA at 500 V conforming to DIN (with fuse) Icn 50 kA at 690 V conforming to DIN (with fuse) Icn 80 kA at 415 V conforming to BS (with fuse) Icm 15 kA at 690 V (without fuse) Icm 22 kA at 415 V (without fuse) Icm 22 kA at 500 V (without fuse)
Suitability for isolation	Yes
Contact position indicator	Yes
Visible break	No
Contact operation	Double-break

Environment

Mechanical durability	10000 Cycles
Electrical durability	AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz
[Icw] rated short-time withstand current	5 KA for 1 s 0.95 KA for 30 s 1.15 KA for 20 s 2.9 KA for 3 s
Design	Horizontal design
Connections terminals	Screw connection
Connections - terminals	Screw connection M8 100 A
Tightening torque	15...22 N.m for terminal
Height	140 Mm
Width	183 Mm
Depth	114.5 Mm
Standards	EN/IEC 60947-5 EN/IEC 60269-1 EN/IEC 60947-3 EN/IEC 60947-1 EN/IEC 60269-4
Product certifications	CCC

IP degree of protection	IP20 conforming to IEC 60529 IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102 IK10 conforming to EN 50102
Pollution degree	3
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**