


# Product data sheet

## Characteristics

# LX1D6Z5

TeSys D - contactor coil - LX1D6 - 20 V AC 50 Hz  
for 80 & 95 A contactor

Price\*: 164.00 USD



### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX1D6
Control circuit type	AC 50 Hz
[Uc] control circuit voltage	20 V AC 50 Hz
Average resistance	1.016 Ohm 68 °F (20 °C)
Product compatibility	LC1D80 LC1D95
Mechanical durability	10 Mcycles
Maximum operating rate	3600 Cyc/H 140 °F (60 °C)

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc 50/60 Hz 131 °F (55 °C) Operational 0.8...1.1 Uc 50 Hz 131 °F (55 °C)
Inrush power in VA	200 VA 50 Hz 0.75 68 °F (20 °C))
Hold-in power consumption in VA	20 VA 50 Hz 0.3 68 °F (20 °C))
Heat dissipation	6...10 W 50/60 Hz

### Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net Weight	0.62 Lb(US) (0.28 kg)

### Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
GTIN	03389110208931
Package weight(Lbs)	0.74 Lb(US) (0.337 kg)
Returnability	No

Packing Units

Package 1 Height	0.570 Dm
Package 1 width	0.880 Dm
Package 1 Length	1.260 Dm

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : End of commercialisation