



Main

Range	New Unica
Product or component type	Switch
Device presentation	Mechanism with zamak fixing frame
Switch function	Intermediate
Device application	Control
Provided equipment	Fixing frame
Colour tint	Beige (RAL 1013)
Quantity per set	10 flow-pack

Complementary

Rated current	10 AX at 250 V AC 50/60 Hz
Electrical durability	20000 Cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	LED, colour: white, current consumption: 0.05 mA
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm ² rigid cable 0...2.5 Mm ² flexible cable
Material	CuZn5 Ag: fixed terminals CuZn15: mobile contact PBT (polybutylene terephthalate) GF31: release button Zamak: fixing frame Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing
Marking	Without marking
Surface finish	Glossy
Fixing mode	Screws or claws
Width	74.5 Mm
Height	74.5 Mm
Depth	37.75 Mm
Embedding depth	24.65 Mm
Net weight	0.0589 Kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C


The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Standards	LV directive IEC 60669-1 RoHS compliant
Product certifications	CE Aenor EAC NF

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Liquid soap Ammonia Alcohol Acetone Window-cleaning fluid Oil Petrol Bleach UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**