

Product data sheet

Characteristics

LX4D7LD

contactor coil - TeSys D - LX4D7 - 200 V DC
standard - for 80 A contactor

Price*: 134.00 USD



Commercial status

This Product is Obsolete : OCT 10, 2020

 This Product is Obsolete

Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX4D7
Control circuit type	DC standard
[Uc] control circuit voltage	200 V DC
Average resistance	1747 Ohm 68 °F (20 °C)
Product compatibility	LC1D80
Mechanical durability	10 Mcycles
Maximum operating rate	3600 Cyc/H 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.1...0.3 Uc 131 °F (55 °C) Operational 0.85...1.1 Uc 131 °F (55 °C))
Time constant	75 Ms
Inrush power in W	22 W 68 °F (20 °C))
Hold-in power consumption in W	22 W 68 °F (20 °C)

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net Weight	1.50 Lb(US) (0.68 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	03389110190021
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : End of commercialisation