




Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 81.90 USD



### Main

Range of product	TeSys D
Range	TeSys
Product or component type	Contactor coil
Device short name	LX4D8
Control circuit type	DC standard
[Uc] control circuit voltage	440 V DC
Average resistance	21501 Ohm at 68 °F (20 °C)
Inductance of closed circuit	684.66 H
Product compatibility	LC1D150 LC1D115
Mechanical durability	8 Mcycles
Operating rate	1200 cyc/h at <= 140 °F (60 °C)

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.15...0.4 Uc at 131 °F (55 °C) drop-out 0.75...1.2 Uc at 131 °F (55 °C) operational
Time constant	25 ms
Inrush power in W	270...365 W at 68 °F (20 °C)
Hold-in power consumption in W	2.4...5.1 W at 68 °F (20 °C)

### Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Product weight	0.66 lb(US) (0.3 kg)

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	003389110115642
Nbr. of units in pkg.	1
Package weight(Lbs)	0.66000000000000003
Returnability	N
Country of origin	CZ

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0847 - Schneider Electric declaration of conformity <a href="#">Schneider-Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause-cancer.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**