



### Main

Range of product	New Unica
Range	New Unica
Device application	Control
Product or component type	Roller blind switch
Device presentation	Mechanism with fixing frame
Switch function	3 positions
Provided equipment	Fixing frame
Colour tint	Anthracite (RAL 7021)
Quantity per set	10 flow-pack

### Complementary

Rated current	6 A, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker and push-button
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm <sup>2</sup> (rigid) 0...2.5 mm <sup>2</sup> (flexible)
Material	Fixing frame : zamak Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Release button : PBT (polybutylene terephthalate) GF30 Terminals : CuZn15
Marking	0 position Arrow
Surface finish	Painted powder coated
Fixing mode	Screws or claws
Width	70.9 mm
Height	70.9 mm
Depth	44.35 mm
Embedding depth	32.8 mm
Product weight	0.069 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	RoHS compliant IEC 60669-1 LV directive
Product certifications	CE Aenor NF EAC
Targeted channel	Professional
Main colour tint	Anthracite

### Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	UV resistant Ammonia Window-cleaning fluid Oil Alcohol Acetone Bleach Liquid soap Petrol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**