



Main

Range	New Unica
Device application	Control
Product or component type	Switch
Device presentation	Mechanism with zamak fixing frame
Switch function	2 x 1-pole 2-way
Number of rocker	2
Provided equipment	Fixing frame
Colour tint	Beige (RAL 1013)
Quantity per set	10 flow-pack

Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	White LED : 0.05 mA
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Fixing frame : zamak Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Without marking
Surface finish	Glossy
Fixing mode	Screws or claws
Width	70.9 mm
Height	70.9 mm
Depth	36.25 mm
Embedding depth	23.15 mm
Product weight	0.0692 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Standards	RoHS compliant IEC 60669-1 LV directive
Product certifications	NF EAC Aenor CE

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Bleach Acetone Oil Ammonia UV resistant Window-cleaning fluid Alcohol Petrol Liquid soap
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**