



### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Range of product	TeSys F
Range	TeSys
Product or component type	Contactor coil
Device short name	LX4FH
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F265 LC1F330
Control circuit type	DC wide range
[Uc] control circuit voltage	48 V DC
Average resistance	2.19 Ohm inrush at 68 °F (20 °C) 400 Ohm holding at 68 °F (20 °C)
Inductance of closed circuit	59.5 H
Operating time	40...50 ms closing 40...65 ms opening
Mechanical durability	10 Mcycles
Operating rate	<= 60 cyc/h at <= 55 °C

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.15...0.2 Uc at 131 °F (55 °C) drop-out 0.85...1.1 Uc at 131 °F (55 °C) operational
Inrush power in W	750 W at 68 °F (20 °C)
Hold-in power consumption in W	5 W at 68 °F (20 °C)

### Environment

Ambient air temperature for operation	> 23...131 °F (> -5...55 °C)
Product weight	1.63 lb(US) (0.74 kg)

### Ordering and shipping details

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Nbr. of units in pkg.	1
Package weight(Lbs)	1.6300000000000001
Returnability	N

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0830 - Schneider Electric declaration of conformity <a href="#">Schneider-Electric declaration of conformity</a>
Product environmental profile	Available
Product end of life instructions	Available

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**