



Main

Range	New Unica
Product or component type	Switch
Device presentation	Mechanism with zamak fixing frame
Switch function	2-pole 1-way
Device application	Control
Provided equipment	Fixing frame
Colour tint	Anthracite (RAL 7021)
Quantity per set	10 flow-pack

Complementary


Rated current	16 AX at 250 V AC 50/60 Hz
Electrical durability	20000 Cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	LED, colour: red, current consumption: 1.5 mA
Connections - terminals	Screw terminals
Cable cross section	0...4 Mm ² rigid cable 0...4 Mm ² flexible cable
Material	CuZn5 Ag: terminals Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing
Marking	0 - 1
Surface finish	Painted powder coated
Fixing mode	Screws or claws
Width	74.5 Mm
Height	74.5 Mm
Depth	37.75 Mm
Embedding depth	24.65 Mm
Net weight	0.0603 Kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	LV directive IEC 60669-1 RoHS compliant
Product certifications	CE Aenor EAC NF

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Oil Acetone Window-cleaning fluid Ammonia Liquid soap Alcohol UV resistant Petrol Bleach
Environmental health and issues	Halogen free

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**