

Main

Range	New Unica
Product or component type	Light module
Device presentation	Mechanism with zamak fixing frame
[Ue] rated operational voltage	230 V AC, 50...60 Hz
Number of modules	2 modules
Fixing mode	Screws or claws

Complementary

Colour tint	Anthracite
Light block colour	White
Bulb type	LED
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Material	Casing : PC (polycarbonate) GF10 FR Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30 Mechanism cover : PC Fixing frame : PC (polycarbonate) GF10 FR Rocker switch : thermoplastic ABS-UV stabilised
Standards	CE EN 62094-1
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Embedding depth	21 mm
Depth	31 mm
Width	75 mm
Height	75 mm
Product weight	0.068 kg
Targeted channel	Professional

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IK degree of protection	IK03
IP degree of protection	IP2xC
Environmental characteristic	Oil UV resistant Acetone Liquid soap Ammonia Window-cleaning fluid Bleach Petrol Alcohol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**