



Main

Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica Studio
Device presentation	Complete product
Socket number	2
Outlet poles configuration	2P + E with shutters
Outlet standard	German
Outlet standard description	Side earth

Complementary


Rated current	16 A at 250 V AC
Network frequency	50/60 Hz
Fixing mode	Screws
Colour tint	Beige (RAL 1013)
Connections - terminals	Screw terminals
Cable cross section	0...2.5 Mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 Mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I _n and 1.1 I _{un} , cos phi = 0.6
Electrical durability	10000 Cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	PC: mechanism cover
Surface finish	Glossy
Quantity per set	Set of 1 flow-pack
Standards	IEC 60884-1 UNE 20315-1-1 UNE 20315-1-2 DIN VDE 0620-1
Product certifications	Aenor EAC
Embedding depth	24 Mm
Depth	47 Mm
Width	85 Mm
Height	125 Mm
Net weight	0.099 Kg
Surface treatment	Untreated

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Liquid soap Alcohol Acetone Window-cleaning fluid Petrol UV resistant Oil Bleach Ammonia
Environmental health and issues	Halogen free

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**