



## Main

Range	New Unica
Range of product	New Unica
Device application	Signalling
Product or component type	Electronic doorbell
Device presentation	Mechanism with zamak fixing frame
[Ue] rated operational voltage	230 V AC, 50/60 Hz
Number of modules	2 modules
Fixing mode	Screws or claws
Colour tint	Aluminium

## Complementary

Current consumption	14 mA
Type of setting	5 programmable melodies
Connections - terminals	Screw terminals
Acoustic level	70 dB/1m
Cable cross section	0.75...1.5 mm <sup>2</sup> (flexible) 0.75...1.5 mm <sup>2</sup> (rigid)
Connected auxiliaries	3 indicator lights connected in parallel 10 standard push-buttons connected in parallel
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised
Standards	EN 62080
Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive
Product certifications	CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 mm
Depth	50 mm
Width	75 mm
Height	75 mm
Product weight	0.079 kg
Targeted channel	Professional

## Environment

IK degree of protection	IK04
IP degree of protection	IP20
Environmental characteristic	Ammonia Bleach Alcohol Petrol Acetone Liquid soap UV resistant Window-cleaning fluid Oil
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**