



Main

Range of product	New Unica
Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism
Socket number	1
Outlet poles configuration	2P + E with shutters
Outlet standard	German
Outlet standard description	Side earth

Complementary

Main colour tint	Anthracite
Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² cable(s), 2 - cable stiffness: flexible 0...4 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Casing : PC (polycarbonate) GF10 FR Terminals : CuZn37 Mechanism cover : PC Earth contact : CuZn33
Surface finish	Matt
Quantity per set	Flow-pack : set of 1
Standards	IEC 60884-1 DIN VDE 0620-1 UNE 20315-1-1 UNE 20315-1-2
Product certifications	Aenor EAC
Embedding depth	30.5 mm
Depth	40 mm
Width	45 mm

Height	45 mm
Product weight	0.033 kg
Surface treatment	Painted
Targeted channel	Professional

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Ammonia Alcohol Liquid soap Acetone Window-cleaning fluid Oil Petrol Bleach UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**