



Main

Range	New Unica
Device application	Signalling
Product or component type	Electronic doorbell
Device presentation	Mechanism with zamak fixing frame
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Screws or claws
Colour tint	Anthracite (RAL 7021)

Complementary

Current consumption	14 mA
Type of setting	5 programmable melodies
Connections - terminals	Screw terminals
Acoustic level	70 dB/1m
Cable cross section	0.75...1.5 Mm ² flexible cable 0.75...1.5 Mm ² rigid cable
Connected auxiliaries	3 indicator lights connected in parallel 10 standard push-buttons connected in parallel
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing
Standards	EN 62080
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Product certifications	CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 Mm
Depth	50 Mm
Width	74.5 Mm
Height	74.5 Mm
Net weight	0.079 Kg

Environment

IK degree of protection	IK04
IP degree of protection	IP20
Environmental characteristic	Liquid soap Acetone UV resistant Petrol Bleach Ammonia Oil Window-cleaning fluid Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**