



### Main

Range	New Unica
Product or component type	Switch
Device presentation	Mechanism
Switch function	2-way and OFF retractive
Device application	Control
Colour tint	Aluminium
Quantity per set	10 flow-pack

### Complementary

Rated current	10 A at 250 V AC 50/60 Hz
Electrical durability	20000 Cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	1 module
Pilot light	Without LED
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm <sup>2</sup> rigid cable 0...2.5 Mm <sup>2</sup> flexible cable
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing CuZn37: terminals PBT (polybutylene terephthalate) GF30: release button
Marking	Without marking
Surface finish	Painted powder coated
Fixing mode	Clip-in
Width	22.5 Mm
Height	45 Mm
Depth	34.25 Mm
Embedding depth	21.15 Mm
Net weight	0.0164 Kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	IEC 60669-1 LV directive RoHS compliant
Product certifications	CE Aenor EAC NF

## Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Alcohol Ammonia Bleach Oil UV resistant Liquid soap Acetone Petrol Window-cleaning fluid
Environmental health and issues	Halogen free

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**