



Main

Range	New Unica
Device application	Control
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 2-way
Colour tint	Aluminium
Quantity per set	10 flow-pack

Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Without marking
Surface finish	Painted powder coated
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34.25 mm
Embedding depth	21.15 mm
Product weight	0.0243 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	RoHS compliant IEC 60669-1 LV directive
Product certifications	NF CE Aenor EAC

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Window-cleaning fluid Oil Alcohol Ammonia Petrol Liquid soap Acetone Bleach UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**