



### Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	366 Mm wall: 396 Mm outside:
Height	480 Mm wall: 510 Mm outside:
Depth	86 Mm wall: 21 Mm outside:
Number of 18 mm modules per row	13
Number of horizontal rows	2
Electrical insulation class	Double insulation Class II
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip

### Complementary

Enclosure mounting	Flush
9 mm pitches	26
Total number of 18 mm modules	26
Power dissipation in W	50 W
[In] rated current	63 A
Type of rail	DIN
Cable entry	Side pre-cutouts Cable or tube Removable plates
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	1 earth (Quick) with 24 outgoing
Distribution block outgoing	3 x 25 mm <sup>2</sup> for earth 21 x 4 mm <sup>2</sup> for earth
Enclosure material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	Belgium

## Environment

Fire resistance	Front face: 750 °C Back part: 850 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**