

Main

Range of product	New Unica
Range	New Unica
Device application	Control
Product or component type	Push-button switch
Device presentation	Mechanism
Colour tint	White (RAL 9003)
Quantity per set	10 flow-pack

Complementary

Rated current	10 A, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Light symbol
Surface finish	Glossy
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34.25 mm
Embedding depth	21.15 mm
Product weight	0.0175 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	IEC 60669-1 LV directive RoHS compliant

Product certifications	CE NF Aenor EAC
Targeted channel	Professional
Main colour tint	White

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Oil Ammonia Petrol Acetone UV resistant Liquid soap Alcohol Bleach Window-cleaning fluid
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**