



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	456 Mm wall: 486 Mm outside:
Height	630 Mm wall: 660 Mm outside:
Depth	86 Mm wall: 23 Mm outside:
Number of 18 mm modules per row	18
Number of horizontal rows	3
Electrical insulation class	Double insulation Class II
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip

Complementary

Enclosure mounting	Flush
9 mm pitches	36
Total number of 18 mm modules	54
Power dissipation in W	68 W
[In] rated current	125 A
Type of rail	DIN
Cable entry	Cable or tube Side pre-cutouts Removable plates
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	1 earth (Quick) with 38 outgoers
Distribution block outgoers	6 x 25 mm ² for earth 32 x 4 mm ² for earth
Enclosure material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	Belgium

Environment

Fire resistance	Front face: 750 °C Back part: 850 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**