



## Main

|                           |                             |
|---------------------------|-----------------------------|
| Range                     | New Unica                   |
| Product or component type | USB charger                 |
| Device presentation       | Mechanism with fixing frame |

## Complementary

|                                       |   |
|---------------------------------------|---|
| Device application                    | Charger   |
| Device mounting                       | Flush   |
| Number of modules                     | 2 modules   |
| Colour tint                           | Aluminium   |
| [Ue] rated operational voltage        | 100...240 V AC 50/60 Hz   |
| Maximum power consumption in W        | 0.075 W   |
| Nominal output power                  | 12 W  |
| Input power                           | 12 W  |
| Service life in hours                 | 30000 H 12 W  |
| Socket number                         | 2   |
| Integrated connection type            | 1 USB type A 5 V DC, maximum load current: 2.4 A<br>1 USB type C 5 V DC, maximum load current: 2.4 A  |
| Material                              | ABS (acrylonitrile butadiene-styrene): centre plate<br>PC (polycarbonate) GF10 FR: casing<br>PC (polycarbonate) GF10 FR: internal cover                                       |
| Protection type                       | Short-circuit protection  |
| Number of terminals                   | 2 screw terminals   |
| Clamping connection capacity          | 2 x 0.75...2 x 2.5 mm <sup>2</sup> for rigid cable(s)<br>2 x 0.75...2 x 2.5 mm <sup>2</sup> for flexible cable(s)<br>2 x 0.75...2 x 2.5 mm <sup>2</sup> for stranded cable(s) |
| Wire stripping length                 | 8 Mm  |
| Product compatibility                 | All devices fulfilling the EN 62684 standard  |
| Fixing mode                           | By claws<br>By screws   |
| Type of packing                       | Flow-pack   |
| Ambient air temperature for operation | 0...40 °C   |
| Ambient air temperature for storage   | -5...50 °C  |
| Standards                             | EN 62684<br>ETSI EN 301 489-4<br>EN 60950-1   |
| Height                                | 45 Mm   |
| Width                                 | 22.5 Mm   |
| Depth                                 | 42 Mm   |
| Embedding depth                       | 30.8 Mm   |

## Environment

|                              |                                    |
|------------------------------|------------------------------------|
| Electrical insulation class  | Class II                           |
| Environmental characteristic | REACH Regulation (EC) No 1907/2006 |
| IK degree of protection      | IK04                               |
| IP degree of protection      | IP20                               |

Product Life Status : **Commercialised**