



## Main

Range of product	New Unica
Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism with zamak fixing frame
Socket number	1
Outlet poles configuration	2P with shutters
Outlet standard	European
Outlet standard description	Unearthed

## Complementary

Main colour tint	Anthracite
Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Screws or claws
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> cable(s), 2 - cable stiffness: flexible 0...4 mm <sup>2</sup> cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Fixing frame : zamak Casing : PC (polycarbonate) GF10 FR Terminals : CuZn37 Mechanism cover : PC
Surface finish	Matt
Quantity per set	Flow-pack : set of 1
Standards	IEC 60884-1 NF C 61-314 UNE 20315-1-1 UNE 20315-1-2
Product certifications	EAC NF Aenor
Embedding depth	27.5 mm
Depth	37 mm
Width	70.9 mm

Height	70.9 mm
Product weight	0.0615 kg
Surface treatment	Painted
Targeted channel	Professional

## Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Oil UV resistant Acetone Liquid soap Alcohol Petrol Bleach Ammonia Window-cleaning fluid
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**