



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	396 Mm
Height	330 Mm wall: 360 Mm outside:
Depth	41 Mm outside: 86 Mm wall:
Number of 18 mm modules per row	13
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Provided equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type of front cover	Opaque

Complementary

Enclosure mounting	Flush
9 mm pitches	26
Total number of 18 mm modules	13
Power dissipation in W	34 W
[In] rated current	63 A
[Ui] rated insulation voltage	800 V
Type of rail	DIN
Cable entry	Side pre-cutouts Cable or tube Removable plates
Number of terminal blocks	1 earth (Quick) with 14 outgoers 1 neutral (Quick) with 14 outgoers
Distribution block outgoers	3 x 25 mm ² for earth 11 x 4 mm ² for earth 3 x 25 mm ² for neutral 11 x 4 mm ² for neutral
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic

Colour	Door: white (RAL 9016) Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Market segment	Small commercial Residential

Environment

Fire resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**