

Product data sheet

Characteristics

QO330L100GNYC

QO LoadCenter, Main Lug, 100A, 3PH, 30 SP, NEMA 1, NYC Special Current Density



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 620.00 USD



Main

Product or component type	Load Center
Range of product	QO
Load center type	Main lugs
Line Rated Current	100 A
Number of spaces	30
Short-circuit current	65 kA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	3 phases

Complementary

NEMA degree of protection	NEMA 1 indoor
Cover type	Order separately
Device composition	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	3-wire 4-wire
Material	Tin plated copper busbar
Enclosure material	Welded sheet steel
Surface finish	Baked enamel grey
Height	29.84 in (758 mm)
Width	15.31 in (389 mm)

Ordering and shipping details

Category	00011 - QO 3PH LOAD CENTER,INDOOR
Discount Schedule	DE3
GTIN	00785901295495
Nbr. of units in pkg.	1
Package weight(Lbs)	17.390000000000001
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1248 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**