

Product data sheet

Characteristics

QO330MQ150RB

LOAD Center QO RB MB 150A 3PH 30 CIRCUIT



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price*: 2147.00 USD



Main

Range of product	QO
Product or component type	Load Center
Enclosure type	Weatherproof enclosure
Cover type	Surface cover

Complementary

Load center type	Main breaker
Line Rated Current	150 A
Number of spaces	30
Short-circuit current	25 KA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	3 phase
[Ue] rated operational voltage	208Y/120 V AC 240/120 V delta AC 240 V delta AC
AWG gauge	AWG 4...300 kcmil aluminium/copper
Electrical connection	Lugs
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	4-wire 3-wire
Material	Tin plated copper busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel Gray
Box number	14R
Maximum Height	39.37 In (1000 mm)
Width	14.76 In (375 mm)

Environment

NEMA degree of protection	NEMA 3R outdoor
Ambient air temperature for operation	23 °F (-5 °C) 104 °F (40 °C)
Product certifications	UL Listed

Ordering and shipping details

Category	00017 - QO 3PH LOAD CENTER,OUTDOOR
Discount Schedule	DE3
GTIN	00785901290605
Nbr. of units in pkg.	1
Package weight(Lbs)	47.08 Lb(US) (21.36 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.42 Ft (0.127 m)
Package 1 width	1.28 Ft (0.389 m)
Package 1 Length	3.43 Ft (1.044 m)

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**