

Main

Range of product	New Unica
Range	New Unica
Device application	Control
Product or component type	Switch
Device presentation	Mechanism with zamak fixing frame
Switch function	Intermediate
Provided equipment	Fixing frame
Colour tint	Anthracite (RAL 7021)
Quantity per set	10 flow-pack

Complementary

Rated current	10 AX, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Fixing frame : zamak Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Fixed terminals : CuZn5 Ag Mobile contact : CuZn15 Release button : PBT (polybutylene terephthalate) GF31
Marking	Without marking
Surface finish	Painted powder coated
Fixing mode	Screws or claws
Width	70.9 mm
Height	70.9 mm
Depth	37.75 mm
Embedding depth	24.65 mm
Product weight	0.0571 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	RoHS compliant IEC 60669-1 LV directive
Product certifications	Aenor EAC CE NF
Targeted channel	Professional
Main colour tint	Anthracite

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Liquid soap UV resistant Petrol Alcohol Ammonia Bleach Window-cleaning fluid Oil Acetone
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**