

Main

Range of product	New Unica
Range	New Unica
Device application	Control
Product or component type	Push-button switch
Device presentation	Mechanism with zamak fixing frame
Provided equipment	Fixing frame
Colour tint	Beige (RAL 1013)
Quantity per set	10 flow-pack

Complementary

Rated current	10 A, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Fixing frame : zamak Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Without marking
Surface finish	Glossy
Fixing mode	Screws or claws
Width	70.9 mm
Height	70.9 mm
Depth	34.25 mm
Embedding depth	21.15 mm
Product weight	0.0586 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C

Standards	IEC 60669-1 RoHS compliant LV directive
Product certifications	CE Aenor NF EAC
Targeted channel	Professional
Main colour tint	Beige

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	UV resistant Alcohol Ammonia Acetone Oil Petrol Window-cleaning fluid Bleach Liquid soap
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**