



## Main

Range	Odace
Product or component type	Switch
Device presentation	Mechanism with plastic fixing frame + claws
Switch application	Roller blind
Switch additional information	Mechanical and electrical interlock between up/down
Type of packing	Flow-pack and cardboard with eurohole
Quantity per set	Set of 4


## Complementary

Device mounting	Flush
Switch function	3 positions
Number of rocker	3
Actuator	Rocker
Fixing mode	By claws By screws
Colour tint	Aluminium
Rated current	6 AX - 250 V AC 50/60 Hz
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un
Number of terminals	3 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> stranded cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> flexible cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> rigid cable(s)
Wire stripping length	12 mm
Material	Centre plate : thermoplastic ABS-UV stabilised Support frame : PBT (polybutylene terephthalate) GF30 Casing : PC (polycarbonate) GF10 FR
Height	71 mm
Width	71 mm
Depth	43 mm
Embedding depth	31.2 mm
Product weight	0.048 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**