



### Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	456 Mm wall: 486 Mm outside:
Height	480 Mm wall: 510 Mm outside:
Depth	86 Mm wall: 43 Mm outside: 43 Mm 86 Mm
Number of 18 mm modules per row	18
Number of horizontal rows	2
Electrical insulation class	Double insulation Class II
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip
Type of front cover	Customizable Transparent

### Complementary

Enclosure mounting	Flush
9 mm pitches	36
Total number of 18 mm modules	36
Power dissipation in W	62 W
[In] rated current	90 A
Type of rail	DIN
Cable entry	Removable plates Side pre-cutouts Cable or tube
Number of terminal blocks	1 earth (Quick) with 26 outgoing
Distribution block outgoing	2 x 25 mm <sup>2</sup> for earth 24 x 6 mm <sup>2</sup> for earth
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: transparent

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Fire resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1 Door: 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	EN 60695-2-11 IEC 60695-2-11 IEC 60439-3 IEC 60947-7-1 IEC 62262 EN 60439-3 IEC 60529

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**