



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	570 Mm wall: 610 Mm outside:
Height	930 Mm wall: 960 Mm outside:
Depth	30 Mm outside: 95 Mm wall:
Number of 18 mm modules per row	24
Number of horizontal rows	5
Electrical insulation class	Class II Double insulation
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip

Complementary

Enclosure mounting	Flush
9 mm pitches	48
Total number of 18 mm modules	120
Power dissipation in W	133 W
[In] rated current	160 A
Type of rail	DIN
Cable entry	Cable or tube Removable plates Side pre-cutouts
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	1 earth (Quick) with 44 outgoing
Distribution block outgoing	40 x 6 mm ² for earth 1 x 50 mm ² for earth 3 x 25 mm ² for earth
Enclosure material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	France Belgium

Environment

Fire resistance	Front face: 750 °C Back part: 850 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**