



### Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

### Main

Rated power in W	2700 W
Rated power in VA	3000 VA
Nb of power socket outlets	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Output voltage	230 V
Output voltage	220 V 240 V
Input voltage	220 V 240 V
Input voltage	230 V
Plug standard	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British
Number of rack unit	0U
Number of cables	1

### General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Cloud-enabled monitoring
Redundant	No
Provided equipment	USB cable

### Physical

Mounting location	Front
Mounting mode	Not rack-mountable
Mounting preference	No preference
Depth	54.4 Cm
Height	43.5 Cm

Net weight	52.5 Kg
Width	19.7 Cm
Two post mountable	0
USB compatible	Yes
Colour	Black

### Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

### Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2700 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

### Conformance

Product certifications	CE EAC RCM VDE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

### Environmental

Acoustic level	53 dBA
Heat dissipation	375 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery type	Lead-acid battery
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery power in VAH	816 VAh runtime
Battery charger power	271 W rated

### Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1

## Surge Protection and Filtering

Surge energy rate	365 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Package 1 Weight	63.7 Kg
Package 1 Height	69.9 Cm
Package 1 width	38.1 Cm
Package 1 Length	76.2 Cm
Number of Units in Package 3	9

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Product Life Status : **Commercialised**