



### Main

Range of product	Zelio Relay
Product or component type	Solid state relay
Device short name	SSL
Network number of phases	1 phase

### Complementary

Mounting support	Spring socket
[In] rated current	0.1 A
Output voltage	1...48 V DC
[Uc] control circuit voltage	16...30 V DC
Contacts type and composition	1 NO
Tightening torque	10...40 N.m
Connections - terminals	Flexible cable with cable end : 0.2...1.5 mm <sup>2</sup> (AWG 24...AWG 16) Solid cable with cable end : 0.2...1.5 mm <sup>2</sup> (AWG 24...AWG 16)
Capacitance unbalance	1.5 pF input/output
Minimum switching voltage	16 V DC turn-on
Maximum switching voltage	5 V DC turn-off
Input impedance	3.43 kOhm
Solid state output type	DC switching Transistor output
Load current	0.001...0.1 A
Absolute maximum voltage	60 V DC
Surge current	0.3 A for 10 ms
Voltage drop	<= 1 V on-state
Leakage current	<= 0.001 mA off-state
Response time	0.25 ms turn-on 0.12 ms turn-off
Overvoltage category	III
Width	6.2 mm
Height	104.6 mm
Depth	79.5 mm
Product weight	0.0285 kg
Device presentation	Complete product

## Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	2500 V for input/output
Pollution degree	2
Standards	EN 61984 IEC 60950-1 IEC 61000 IEC 62314 IEC 61984
Product certifications	UL 508 CE GOST UL CSA22.2 No. 14-10 RoHS CSA REACH
Marking	CURus EAC CE CSA China RoHS
IP degree of protection	IP20
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-20...85 °C


## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1417 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------


Dimensions



---

Derating Curves

---



A : Load Current (Amperes)  
B : Ambient Temperature (°C)

Product Life Status : **Commercialised**