

Product data sheet

Characteristics

SSP03EMA32S

Surge Protect - EMA - 320kA - 240/120VAC delta
- 3P4W - T4X



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Surge protection device
Range of product	SurgeLogic
Device short name	EMA

Complementary

Surge current	320 kA
System Voltage	240/120 V delta AC
Phase	3 phases
Wiring configuration	4-wire
Connections - terminals	Lugs AWG 10...AWG 2 copper Torque to: 35.4 lbf.in (4 N.m)
[Uc] maximum continuous operating voltage	150 V
Nominal discharge current	20 kA
Short-circuit protection	200 kA
Local signalling	Status LED, green = normal operation per phase Status LED, red = fault per phase
Provided equipment	Surge counter Alarm enable/disable switch Dry contacts
Device mounting	Surface
Height	22.67 in (575.8 mm)
Width	11.7 in (297.2 mm)
Depth	9.4 in (238.8 mm)

Environment

NEMA degree of protection	NEMA 4X
Enclosure material	Stainless steel
Standards	UL 1283 ed. 5 UL 1449 ed. 4 CSA C22.2 No 8
Ambient air temperature for operation	149 °F (65 °C)

Ordering and shipping details

Category	08464 - SURGE PROTECTION EMA
Discount Schedule	DE1B
Nbr. of units in pkg.	1
Package weight(Lbs)	45.200000000000003
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**