



Main

Product or component type	Uninterruptible power supply (UPS)
Provided equipment	Software CD 1 USB cable 1 RS232 User manual 1 Cable 1 Power cable 1
Mounting support	Floor-standing
Communication port protocol	USB SmartSlot RS232
Reset	Automatic reset
Function available	Battery monitoring Energy efficiency Audible alarm when a fault condition arises Intelligent charging algorithm monitors battery and AC supply Internal bypass With LCD display Optional communication kit for remote monitoring
Topology	Double conversion online

Complementary

Display type	LCD display
Integrated connection type	USB port Serial link
Energy values	600 J
Type of signal	Sine wave
Protection device type	Miniature circuit breaker (MCB) Surge protection device (SPD)
Protection type	Power factor variation Surge arrester Circuit breaker
Input voltage	220 V AC 230 V AC nominal mode 240 V AC
Output voltage	230 V AC on nominal mode 220 V AC 240 V AC
IP degree of protection	IP20
Transfer time	0 s
Network frequency	40...70 Hz
Power range	800 W 1000 VA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Crest factor	3:1
Electrical connection	1 inlet (input) IEC 320 C14 3 outlet (output) IEC 320 C13
Local signalling	Alarm distinctive (low battery) LCD display continuous or intermittent tone (overload)
Efficiency	88 %
Battery type	Lead-acid battery
Number of batteries	3
Charging time	4 h
Battery voltage	12 V
Battery life	5 yr
Quantity per set	Set of 1
Product weight	9.3 kg
Height	223 mm
Width	145 mm
Depth	288 mm

Environment

Acoustic level	< 50 dBA
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...50 °C
Standards	IEC 62040-1-1 IEC 62040-1-2
Product certifications	CE

Contractual warranty

Warranty period	2 years
-----------------	---------

Product Life Status :	Commercialised
-----------------------	----------------