



by Schneider Electric

Easy PDU Switched Rack Power Distribution Unit

Overview

EPDU1116S, EPDU1132S


The APC by Schneider Electric Easy PDU, Switched Rack Power Distribution Unit may be used as a stand-alone, network-manageable power distribution device. The Easy PDU measures the current that it and its attached devices use. Manage your Easy PDU through its Web User Interface (Web UI), or Simple Network Management Protocol (SNMP).

Display Interface. The liquid crystal display (LCD) and function button allow you to monitor voltage, current, and power factors of attached devices. Remote communication can be established through the network port. Environment is monitored through the temperature and humidity (T/H) port.

Outlets. EPDU1116S: Twenty (20) C13 10A outlets and four (4) C19 16A outlets
EPDU1132S: Bank 1: Ten (10) C13 10A outlets and two (2) C19 16A outlets
Bank 2: Ten (10) C13 10A outlets and two (2) C19 16A outlets

Power cord. EPDU1116S: The power cord is 3 m (9.8 ft) in length.
EPDU1132S: The power cord is 3 m (9.8 ft) in length.

Mounting. Brackets: The Rack PDUs can be mounted to a rack using the two (2) brackets and mounting hardware provided.
Toolless Mounting: Two (2) mounting pegs are installed on the back sides of the Rack PDUs for 0U mounting capability in a rack or enclosure.



EPDU1116S



EPDU1132S

Specifications

	EPDU1116S	EPDU1132S
Electrical		
Nominal Input Voltage	200 - 240 VAC 1 PHASE	
Maximum Input Current (Phase)	16A	32A
Input Frequency	50/60Hz	
Input Connection	IEC309 16A	IEC309 32A
Output Voltage	200 - 240 VAC	
Output Connections	<p>Twenty (20) C13 Max. output current 10A</p> <p>Four (4) C19 Max. output current 16A</p>	<p>Bank 1: Ten (10) C13 Max. output current 10A Two (2) C19 Max. output current 16A</p> <p>Bank 2: Ten (10) C13 Max. output current 10A Two (2) C19 Max. output current 16A</p>
Circuit Breakers	None	Two (2) 16A 1-pole hydraulic-magnetic circuit breakers
Physical		
Dimensions (H x W x D)	1738 x 55 x 62 mm (68.43 x 2.16 x 2.44 in)	
Input power cord length	3 m (9.8 ft)	
Shipping dimensions (H x W x D)	1950 x 160 x 110 mm (76.77 x 6.30 x 4.33 in)	
Weight/Shipping weight EPDU1116S EPDU1132S	7.3 kg (16.09 lb)/8.5 kg (18.74 lb) 7.9 kg (17.41 lb)/9.0 kg (19.84 lb)	
Environmental		
Maximum elevation (above MSL) Operating/Storage	0–3000 m (0–10,000 ft) / 0–15000 m (0–50,000 ft)	
Temperature: Operating/Storage	–5 to 45°C (23 to 113°F)/ –25 to 65°C (–13 to 149°F)	
Humidity: Operating/Storage	5–95% RH, non-condensing	
Compliance		
EMC verification	CE EN55035, EN55032, EN55024	
Safety verification	CE, TUV, EN/IEC62368-1	
CE EU Contact Address	Schneider Electric, 35 rue Joseph Monier 92500 Rueil Malmaison France	
Environmental	RoHS & Reach	

Customer support and warranty information are available on the APC by Schneider Electric website, www.apc.com.

© 2020 APC by Schneider Electric. APC and the APC logo are owned by Schneider Electric S.E. All other trademarks are property of their respective owners.

990-6321
3/2020