

Facility Planning Data Sheet

MGE Galaxy 4000



RATINGS OF CABLES AND OVERCURRENT DEVICES SUPPLIED FOR INFORMATION ONLY. USER TO CONSULT WITH THEIR ENGINEERING SERVICES BEFORE ADOPTING.

UPS Rating		UPS AC Input						Battery System			AC Output		Mechanical Data			
		Voltage		Current		Recommended Input AWG	Rec. OCPD	Nominal VDC	Battery kW	Current @ Nom. V	Current @ Full Load		Typical Dimensions HxWxD	Average Weight Lbs.	Floor Loading Lbs/Ft ²	Heat Rejection BTU/Hr
		Input	Output	Full Load	Max.						Max.	OCPD				
kVA	kW															
40	32	208	208	102	121	1/0	150	240	36	157	111	150	34x72x36	1,060	125	14,900
50	40	208	208	127	150	2/0	175	240	46	196	139	175	34x72x36	1,060	125	18,700
65	56	208	208	166	195	250 MCM	250	240	59	256	180	250	34x72x36	1,235	145	24,200
75	60	208	208	191	225	350 MCM	300	240	68	294	208	300	34x72x36	1,235	145	28,000

1. Input current based on full rated output load.
2. Maximum (Max.) current is for duration of battery recharge.
3. Input and bypass cables must be run in separate conduits from output cables. Not more than three conductors in raceway assumed; ambient temperature of 86°F assumed.
4. If initial load is less than UPS' rated output, it is recommended that AC input, battery, and AC output wiring and overcurrent protection be sized to UPS' full load rating to accommodate possible future expansion.
5. Nominal battery voltage is shown at 2.0 volts/cell per NEC 480-2.
6. DC cables should be sized for a total maximum of less than 1% of CB rating.
7. OCPD = Overcurrent Protection Device. Recommended represents 125% of nominal full load current (continuous) per NEC 215.
8. Minimum-sized grounding conductors to be per NEC 250-122. Parity-sized ground conductors are recommended. Neutral conductors to be sized for full capacity per NEC 310-15(b)(4).

9. Wiring requirements:
 - AC Input/Output: 3Ø, 3 or 4 wire + ground, depending on UPS configuration. See Installation Manual and submittal drawings for specific instructions.
 - DC Input: 2 wire (positive and negative) + ground
10. All wiring to be in accordance with all applicable national and/or electrical codes
11. Minimum access clearance per UPS drawings.
12. Top or bottom cable entry through removable access plates. Punch plates to suit conduit size, then replace.
13. Control wiring and power wiring must be run in separate conduit.
14. Weights and dimensions shown do not include battery cabinet(s), distribution cabinet(s), or other options.
15. Backup emergency generator must be properly sized for UPS application and equipped with an isochronous governor for frequency regulation, and a UPS-compatible voltage regulator for voltage stability.
16. If site configuration requires an external maintenance bypass, phase parity between UPS input and UPS bypass must be ensured. Consult MGE applications engineer.
17. References are per NEC 1999. Consult local codes for possible variations.

Additional Notes:

A. Temperature rating of conductors: 90°C (194°F). Reference NEC Table 310- 16, 75°C column, using copper conductors. 75°C (167°F) cable terminal conductors assumed.